

FD3-AG432J00TBBP4-US



Standard FDH3000, 432F loaded pad/vault mounted cabinet, SC/APC, PNP splitter capable, OSP Dry Dielectric Flat Ribbon Cable, 100 ft stubs, using a 3x144F distribution cable assembly and a 1x48F feeder, Build America Buy America (BABA) Compliant

- *CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000
Government Funding	Build America Buy America (BABA) coming soon*

General Specifications

Access	Front
Cable Type	Dry Dielectric - Ribbon
Color	Putty white
Distribution Cables, quantity	3
Distribution Ports, quantity	432
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	48
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	30

Dimensions

Height	1,066.8 mm 42 in
Width	685.8 mm 27 in
Depth	457.2 mm 18 in

FD3-AG432J00TBBP4-US

Cable Length 30.48 m | 100 ft

Enclosure Size Medium

Material Specifications

Finish Powder coated

Material Type Aluminum

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

