

A-100454

Base Product



Single Phase Meter Pillar Cabinet

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type

Power supply enclosure

General Specifications

Access

Front door

Accessories

Cable plate | In-ground root

Batteries Supported

0

Batteries Supported, with optional battery pedestal

0

Cabinet Type

Meter cabinet

Color

Gray | Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

Door Security

7 mm triangle lock

Internal Mounting Surface

12 mm plywood backboard

Dimensions

Height

863.6 mm | 34 in

Width

381 mm | 15 in

Depth

177.8 mm | 7 in

Depth, without door

177.8 mm | 7 in

Electrical Specifications

ac Distribution Type

6-way metal enclosure

ac Feeds, Outgoing, quantity

4

Generator Connection

No connection

Power Phase

Single

Voltage

230 Vac

Material Specifications

A-100454

Finish Powder coated

Material Type Galvanized steel

Packaging and Weights

Weight, net 19.958 kg | 44 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system