

1-1671365-1



Fiber Optic Termination Panel, 1U, 19 in, modular, unloaded, no cover, black

OBSOLETE

Replaced By:

760242453
AGL-1U-SL

AGILE 1U sliding panel, accepts (4) G2 modules or adapter packs providing up to 48 duplex LC or 32 MPO ports

Product Classification

Regional Availability	Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber patch panel

General Specifications

Body Style	Symmetrical
Color	Black
Color, front	Black
Growth Configuration	Unloaded
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	4
Rack Type	EIA 19 in
Rack Units	1

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	258.6 mm 10.181 in

Material Specifications

Finish	Powder coated
Material Type	Hot deep galvanized steel

1-1671365-1

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1