


# SD-003-KIT2



## Static Desiccator Dehydrator, with remote mounting accessories kit

- To meet our global customer's RoHS environmental needs, we have changed our desiccant to a cobalt-chloride free desiccant. The compliant desiccant is orange when dry and turns green when saturated

### OBSOLETE

This product was discontinued on: September 1, 2023

## Product Classification

**Product Type** Dehydrator

## General Specifications

**Dehydrator Type** Desiccant  
**Desiccant Capacity** 283 liters (10 cu ft) at 80% RH, +20 °C  
**Mounting** Pole  
**Port Count** 1  
**Port Type** 3/8 in PE tube x 1/8 NPT

## Dimensions

**Product Height** 127 mm | 5 in  
**Product Width** 50.8 mm | 2 in  
**Product Depth** 50.8 mm | 2 in  
**Volume Capacity, maximum** 0.028 m<sup>3</sup> | 0.999 ft<sup>3</sup>  
**Volume Capacity, minimum** 0 m<sup>3</sup> | 0 ft<sup>3</sup>

## Environmental Specifications

**Operating Temperature** -29 °C to +49 °C (-20 °F to +120 °F)

## Packaging and Weights

# SD-003-KIT2

---

<b>Height, packed</b>	203.2 mm   8 in
<b>Width, packed</b>	203.2 mm   8 in
<b>Depth, packed</b>	63.5 mm   2.5 in
<b>Included</b>	3/8 in polyethylene tubing   90° elbow fitting   Instruction sheet   Polyethylene splice union fitting   Static desiccator
<b>Weight, gross</b>	0.9 kg   1.984 lb
<b>Weight, net</b>	0.2 kg   0.441 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

