7761306-00 | DCM AF 7524L



Node A+/ Node AM Digital Channel Module (DCM) medium power for LTE 700

Product Classification

Regional Availability EMEA

Product Type RF repeater unit

Electrical Specifications

Electrical Safety Standard EN 62368-1

Gain, typical80 dBGain Adjustment Range30 dBLicense BandLTE 700

Power Consumption 70 W

Electrical Compliance EN 301908-15

Electrical Specifications, Rx (Uplink)

Operating Frequency Band 703 – 733 MHz

Output Power @ One Carrier27 dBmOutput Power @ Two Carriers24 dBm

Electrical Specifications, Tx (Downlink)

Operating Frequency Band 758 – 788 MHz

Output Power @ One Carrier24 dBmOutput Power @ Two Carriers21 dBm

Environmental Specifications

Operating Temperature -33 °C to +55 °C (-27.4 °F to +131 °F)

Ingress Protection Test Method IEC 60529:2001, IP65

Packaging and Weights

Weight, net 3 kg | 6.614 lb



7761306-00 | DCM AF 7524L

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

