

# 5-555174-3

---

Modular Plug, 6P/6C, unshielded, flat oval, 6-position, category 5, Indonesian, 50 pcs

## OBSOLETE

This product was discontinued on: August 14, 2018

### Replaced By:

6-554720-5  
MP-88U-F-2

Modular Plug, 8P/8C, unshielded, flat oval, 8-position, category 5, Indonesia, 50 pcs

## Product Classification

<b>Regional Availability</b>	Asia
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Modular plug

## General Specifications

<b>ANSI/TIA Category</b>	5
<b>Cable Type</b>	Flat oval, unshielded
<b>Conductor Type</b>	Stranded
<b>Interface</b>	RJ12
<b>Positions/Loaded Contacts</b>	6/6
<b>Termination Type</b>	IDC

## Dimensions

<b>Compatible Cable Diameter, maximum</b>	6.85 mm   0.27 in
<b>Compatible Cable Diameter, minimum</b>	2.79 mm   0.11 in

## Electrical Specifications

<b>Current Rating, maximum</b>	0.75 A
<b>Insulation Resistance, minimum</b>	500 mOhm
<b>Safety Voltage Rating</b>	150 Vac

## Material Specifications

<b>Contact Base Material</b>	Phosphor Bronze
<b>Material Type</b>	Glass filled polycarbonate

# 5-555174-3

---

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

**Flammability Rating** UL 94 V-2

## Packaging and Weights

**Packaging quantity** 50

**Packaging Type** Bag | Box | Carton