## AT-20-43-MF



#### 20 dB Coaxial Attenuator DC-6000 4.3-10 M-F

#### **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Attenuator

#### General Specifications

Device TypeAttenuatorApplicationIndoorColorSilverInner Contact PlatingSilver

Interface4.3-10 MaleInterface 24.3-10 Female

Outer Contact Plating Trimetal

### **Electrical Specifications**

Return Loss, minimum20.8 dBAttenuation20 dBAttenuation Tolerance±0.6 dBAverage Power, maximum2 WImpedance50 ohm

**Operating Frequency Band** 0 – 6000 MHz

Peak Power, maximum 0.5 kW VSWR 1.2

#### **Environmental Specifications**

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

Regulatory Compliance/Certifications



# AT-20-43-MF

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

