

204679A-9



Boot Assembly, 4 in, for 3 in corrugated coaxial cable

OBSOLETE

Product Classification

Product Type	Boot assembly
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Corrugated
Cables per Cushion	1
Color	Black

Dimensions

Height	101.6 mm 4 in
Length	76.2 mm 3 in
Nominal Size	3 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Environmental Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	≥1000 hours
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66

Packaging and Weights

204679A-9

Height, packed	149.86 mm 5.9 in
Width, packed	149.86 mm 5.9 in
Length, packed	78.74 mm 3.1 in
Included	Boot Cushion Two clamps
Packaging quantity	1
Weight, gross	0.64 kg 1.411 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

