



Cold shrink Kit for 22.1 mm (0.87 in) to 7.37 mm (0.29 in) connections

## Product Classification

<b>Product Type</b>	Cold shrink kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Application</b>	Provides additional moisture seal for cable connections
<b>Color</b>	Black

## Dimensions

<b>Width</b>	53.848 mm   2.12 in
<b>Length</b>	254 mm   10 in
<b>Cable Diameter for Seal, maximum</b>	22.1 mm   0.87 in
<b>Cable Diameter for Seal, minimum</b>	7.37 mm   0.29 in
<b>Inner Diameter</b>	51.31 mm   2.02 in

## Material Specifications

<b>Material Type</b>	EPDM rubber
----------------------	-------------

## Environmental Specifications

<b>UV Resistance Test Method</b>	UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours
<b>Weather Resistance Test Method</b>	04AS00-03.6.0   IEC 60529:2001, IP67   MIL-STD-1344A, Method 1002

## Packaging and Weights

<b>Height, packed</b>	292.1 mm   11.5 in
<b>Width, packed</b>	78.74 mm   3.1 in

# 241475-13

---

<b>Length, packed</b>	78.74 mm   3.1 in
<b>Included</b>	One EPDM rubber tube   One sealing foam strip
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.16 kg   0.353 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

