# 896761-000 | T-DUX-35



#### TDUX - Inflatable Duct Seal, size 1

- Flexible and reliable wraparound inflatable sealing system for cables
- Fast and easy to install or remove, even when water is flowing out of the duct
- Independent of duct or cable ovality
- Water and airtight up to 50 kPa (7 psi)
- Environmentaly friendly, non-toxic and resistant to chemicals

#### **Product Classification**

Regional Availability Latin America | North America

Product Type Cable duct seal

Product Series TDUX

Ordering Note When sealing more than two cables in a duct, seperate orderable TDUX-CL clips are to be

used

#### **Dimensions**

 Width
 120 mm | 4.724 in

 Length
 155 mm | 6.102 in

 Cable Diameter, maximum
 25 mm | 0.984 in

 Cable Diameter, minimum
 12 mm | 0.472 in


 Conduit Inner Diameter, maximum
 35 mm | 1.378 in

 Conduit Inner Diameter, minimum
 25 mm | 0.984 in

### Dimension Drawing



# 896761-000 | T-DUX-35



### **Environmental Specifications**

Installation temperature  $-5 \,^{\circ}\text{C}$  to +40  $^{\circ}\text{C}$  (+23  $^{\circ}\text{F}$  to +104  $^{\circ}\text{F}$ )

Packaging and Weights

**Included** Inflatable bladder with sealing mechanism

Packaging quantity 10

## Regulatory Compliance/Certifications

Compliant

| Agency     | Classification  |
|------------|---|
| CHINA-ROHS | Below maximum concentration value                                     |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |

