

# BC-30-10

---



Pipe-to-Pipe Clamp, heavy duty, joins two 1-1/2 in to 3-1/2 in OD round members

## Product Classification

**Product Type** Clamp set

## General Specifications

**Mounting** Pipe-to-pipe

**Taper Taper** Tapered

## Dimensions

**Height** 50.8 mm | 2 in

**Width** 152.4 mm | 6 in

**Length** 254 mm | 10 in

**Mounting Diameter, maximum** 88.9 mm | 3.5 in

**Mounting Diameter, minimum** 38.1 mm | 1.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamp halves | Threaded rod

**Packaging quantity** 2

**Weight, net** 5.4 kg | 11.905 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant

# BC-30-10

---

UK-ROHS

Compliant

