

# LUHG-38

---



Lace-up Hoisting Grip for HELIAX® 0.40-0.56 in (10.2-14.2 mm) cable including all RFFT discrete trunk series cables

## Product Classification

<b>Product Type</b>	Hoisting grip
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® standard product (Global)

## General Specifications

<b>Attachment Spacing Intervals</b>	60.96 m   200 ft
<b>Hoisting Grip Type</b>	Lace-up hoisting grip
<b>Installation Tool</b>	Required, not included
<b>Support Clamp</b>	Not included
<b>Tool Type</b>	Hoisting grip

## Dimensions

<b>Grip Length, minimum</b>	152.4 mm   6 in
<b>Leader Length, minimum</b>	165.1 mm   6.5 in
<b>Compatible Diameter, maximum</b>	14.2 mm   0.559 in
<b>Compatible Diameter, minimum</b>	10.2 mm   0.402 in
<b>Nominal Size</b>	3/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

## Mechanical Specifications

<b>Pull Load Capacity</b>	90.718 kg   200 lb
---------------------------	--------------------

# LUHG-38

---

## Packaging and Weights

<b>Height, packed</b>	55.88 mm   2.2 in
<b>Width, packed</b>	266.7 mm   10.5 in
<b>Length, packed</b>	266.7 mm   10.5 in
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.04 kg   0.088 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

