



6-to-1 Unit Splitter, for outdoor cable diameter of 0.41 in

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Unit splitter kit
<b>Ordering Note</b>	Order B sealant separately

## General Specifications

<b>Color</b>	Black
<b>Compatible Interface</b>	LC   LC, keyed   SC   ST

## Dimensions

<b>Height</b>	8.128 mm   0.32 in
<b>Width</b>	20.32 mm   0.8 in
<b>Length</b>	50.8 mm   2 in

## Material Specifications

<b>Material Type, body</b>	Acrylonitrile butadiene styrene (ABS)
----------------------------	---------------------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

## Packaging and Weights

<b>Included</b>	Six unit splitter   Split tube seal   Syringe
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system