A3GMPMPCD

Base Product

Ultra Low Loss ULL TeraSPEED® MPO(Unpinned) to MPO(Unpinned) Pre-terminated Trunk Cable, MPO12, 12-Fiber, LSZH, 12 fiber PmP 2.0 mm /B2ca, Method A

Product Classification

Regional Availability	Europe | Middle East/Africa
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Color, boot A	Black
Color, connector A	Green
Color, boot B	Black
Color, connector B	Green
Construction Type	Stranded
Furcation Color	Yellow
Interface, Connector A	MPO-12/APC Female
Interface, Connector B	MPO-12/APC Female
Jacket Color	Yellow
Polarity	Method A
Fibers per Subunit, quantity	12
Total Fibers, quantity	12

Dimensions

Breakout Length	33 in
Cable Assembly Length Range (m)	3 – 999
Cable Assembly Length Range (ft)	10 – 999

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 12, 2024

A3GMPMPCD

Ordering Tree

BASE CODE	-	J	.	.	.	.	.

Jacket Color	
J	Yellow

Breakout Length / Option	
A	33 inch breakout, no gland
B	33 inch breakout, with gland
C	33 inch breakout, with pulling grip
J	Propel, 23 inch breakout, with cable management clip, no pulling grip
K	Propel, 23 inch breakout, with cable management clip, with pulling grip
1	33/60 inch breakout, no gland
2	33/60 inch breakout, with gland on side A
3	33/60 inch breakout, with pulling grip and gland on side A
4	33/120 inch breakout, no gland
5	33/120 inch breakout, with gland on side A
6	33/120 inch breakout, with pulling grip and gland on side A
8	8 – Propel, 23/60 inch breakout, with cable management clip, no pulling grip
T	33 inch breakout, with gland on side A
U	33 inch breakout, with pulling grip and gland on side A
V	60 inch breakout, no gland
W	60 inch breakout, with pulling grip
P	120 inch breakout, no gland
Q	120 inch breakout, with pulling grip

Length

UOM	
F	Feet
M	Meter

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance	B2ca
Environmental Space	Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 12, 2024

A3GMPMPCD

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 12, 2024