# FST-HS



FST Fiber Optic Splice Tray 12 splice capacity

## Product Classification

| | |
|---|---|
| **Regional Availability** | North America |
| **Product Type** | Fiber splice tray |

## General Specifications

| | |
|---|---|
| **Application** | For use with FDF splice panels |
| **Color** | Black |
| **Splicing Capacity, maximum** | 12 |
| **Splicing Type** | Heat shrink |

## Environmental Specifications

| | |
|---|---|
| **Storage Temperature** | -40 °C to +85 °C (-40 °F to +185 °F) |

## Packaging and Weights

| | |
|---|---|
| **Packaging quantity** | 1 |

## Regulatory Compliance/Certifications

| Agency | Classification |
|---|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 19, 2024