




**SYSTIMAX® InstaPATCH® Cu Exit Orientation  
and Panel Application Guide**

# Typical Panel-Trunk Configurations

## Outlet - RJ45 plug: Single Row Standard Density Flat

- 760118323 M2400-1U-GS
- 760150144 360-IPR-MFTP-E-HD6B-1U-24
- 760151498 360-IPR-MFTP-E-HD6B-2U-48



### Typical Selections:

Link	
<b>B</b>	6
<b>D</b>	12
<b>F</b>	18
<b>G</b>	24

Connector	
<b>A</b>	Outlet – Single Row Standard Density
<b>G</b>	RJ45 Plug - Single Row Standard Density

Orientation	
<b>1</b>	Trident Series Flat
<b>3</b>	Right Series Flat
<b>5</b>	Left Series Flat



1 Trident Series Flat



3 Right Series Flat




5 Left Series Flat

Tip: Use the corresponding selections for plug.

# Typical Panel-Trunk Configurations

## Outlet - RJ45 plug: Single Row Standard Density Angled

- 760118349 M2400A-1U-GS
- 760151290 360-IPR-MFTPA-E-HD6B-1U-24
- 760151746 360-IPR-MFTPA-E-HD6B-2U-48



### Typical Selections:

Link	
<b>B</b>	6
<b>D</b>	12

Connector
<b>A</b> Outlet – Single Row Standard Density
<b>G</b> RJ45 Plug - Single Row Standard Density


Orientation
<b>A</b> Trident Series Angled
<b>C</b> Right Series Angled
<b>E</b> Left Series Angled



**A** Trident Series Angled



**C** Right Series Angled



**E** Left Series Angled

Tip: Use the corresponding selections for plug.

# Typical Panel-Trunk Configurations

## Outlet - RJ45 plug: Dual Row Standard Density Flat

- 760207274 CPP-UDDM-M-1U-24
- 760207282 CPP-UDDM-M-2U-48
- 760187187 360-E-MOD-1U-24




### Typical Selections:


Link	
<b>B</b>	6
<b>D</b>	12
<b>F</b>	18
<b>G</b>	24

Connector
<b>B</b> Outlet – Dual Row Standard Density
<b>H</b> RJ45 Plug - Dual Row Standard Density


Orientation
<b>1</b> Trident Series Flat
<b>2</b> Right Paired Flat
<b>3</b> Right Series Flat
<b>4</b> Left Paired Flat
<b>5</b> Left Series Flat
<b>6</b> Trident Paired Flat




**6** Trident Paired Flat




**1** Trident Series Flat




**2** Right Paired Flat



**3** Right Series Flat



**4** Left Paired Flat



**5** Left Series Flat

Tip: Use the corresponding selections for plug.

# Typical Panel-Trunk Configurations

## Outlet - RJ45 plug: Dual Row Standard Density Angled

760207290 CPPA-UDDM-M-1U-24

760207308 CPPA-UDDM-M-2U-48




### Typical Selections:


Link	
<b>B</b>	6
<b>D</b>	12

Connector
<b>B</b> Outlet – Dual Row Standard Density
<b>H</b> RJ45 Plug - Dual Row Standard Density


Orientation
<b>A</b> Trident Series Angled
<b>B</b> Right Paired Angled
<b>C</b> Right Series Angled
<b>D</b> Left Paired Angled
<b>E</b> Left Series Angled
<b>F</b> Trident Paired Angled




**F** Trident Paired Angled




**A** Trident Series Angled



**B** Right Paired Angled



**C** Right Series Angled



**D** Left Paired Angled




**E** Left Series Angled

Tip: Use the corresponding selections for plug.


# Typical Panel-Trunk Configurations

## Outlet - RJ45 plug: Dual Row High Density Flat


760105429 M4800-1U-GS




6 Trident Paired Flat



1 Trident Series Flat



2 Right Paired Flat




3 Right Series Flat

### Typical Selections:


Link	
<b>D</b>	12
<b>G</b>	24

Connector	
<b>C</b>	Outlet – Dual Row High Density
<b>J</b>	RJ45 Plug - Dual Row High Density


Orientation	
<b>1</b>	Trident Series Flat
<b>2</b>	Right Paired Flat
<b>3</b>	Right Series Flat
<b>4</b>	Left Paired Flat
<b>5</b>	Left Series Flat
<b>6</b>	Trident Paired Flat




4 Left Paired Flat




5 Left Series Flat



6 Trident Paired Flat




1 Trident Series Flat



2 Right Paired Flat



3 Right Series Flat



4 Left Paired Flat




5 Left Series Flat

Tip: Use the corresponding selections for plug.


# Typical Panel-Trunk Configurations

## Outlet - RJ45 plug: Dual Row High Density Angled


760109744 M4800A-1U-GS




F Trident Paired Angled



A Trident Series Angled



B Right Paired Angled




C Right Series Angled

### Typical Selections:


Link	
D	12
G	24

Connector	
C	Outlet – Dual Row High Density
J	RJ45 Plug - Dual Row High Density


Orientation	
A	Trident Series Angled
B	Right Paired Angled
C	Right Series Angled
D	Left Paired Angled
E	Left Series Angled
F	Trident Paired Angled




D Left Paired Angled




E Left Series Angled



F Trident Paired Angled



A Trident Series Angled




B Right Paired Angled



C Right Series Angled



D Left Paired Angled




E Left Series Angled

Tip: Use the corresponding selections for plug.

# Typical Panel-Trunk Configurations

## 1100E Modules

760155739 360-E-KIT-1U  
 760155747 360-E-KIT-2U




### Typical Selections:

Link	
<b>B</b>	6
<b>D</b>	12
<b>F</b>	18
<b>G</b>	24

Connector	
<b>R</b>	360 1100 Evolve Module


Orientation	
<b>1</b>	Trident Series Flat
<b>3</b>	Right Series Flat
<b>5</b>	Left Series Flat



**1** Trident Series Flat



**3** Right Series Flat



**5** Left Series Flat

# Typical Panel-Trunk Configurations

## 1100E Modules

760152785 360-A-E-KIT-1U  
 760152793 360-A-E-KIT-2U




### Typical Selections:

Link	
<b>B</b>	6
<b>D</b>	12

Connector	
<b>R</b>	360 1100 Evolve Module


Orientation	
<b>A</b>	Trident Series Angled
<b>C</b>	Right Series Angled
<b>E</b>	Left Series Angled



**A** Trident Series Angled




**C** Right Series Angled



**E** Left Series Angled




# Modules (1100E)



# Information Outlet Single Row Series (MGS600, HGS620)




# Information Outlet Dual Row Series (MGS600, HGS620)

Left Series Flat/Angled	Trident Series Flat/Angled	Right Series Flat/Angled
		
		
		
		



Additional link counts are not illustrated.

# Information Outlet Dual Row Paired (MGS600, HGS620)




Additional link counts are not illustrated.


# InstaPATCH Onelink 2 x 4



# InstaPATCH Onelink 2 x 6



# RJ45 Plugs Single Row Series (360GS10E, G10FP, G10SP)



Additional link counts are not illustrated.






# RJ45 Plugs Dual Row Series (360GS10E, G10FP, G10SP)



8


Additional link counts are not illustrated.

# RJ45 Plugs Dual Row Paired (360GS10E, G10FP, G10SP)

Left Paired Flat/Angled	Trident Paired Flat/Angled	Right Paired Flat/Angled
		
		
		
		
		

Additional link counts are not illustrated.

## Blunt



Additional link counts are not illustrated.