

760037887 | MODG2-6ST-SM-B2

G2 Modular Bezel with 6 TeraSPEED® Singlemode ST Adapters, No Pigtails

OBSOLETE

Replaced By:

760109447
360DP-6ST-SM

InstaPATCH® 360, TeraSPEED® SYSTIMAX 360 Distribution Adapter Pack 6 ST Blue

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Fiber adapter |
| Product Brand | TeraSPEED® |

General Specifications

| | |
|------------------------------|--------|
| Color | Blue |
| Interface | ST/UPC |
| Total Ports, quantity | 6 |

Dimensions

| | |
|---------------|-------------------|
| Height | 30.48 mm 1.2 in |
| Width | 91.44 mm 3.6 in |
| Depth | 27.94 mm 1.1 in |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications


| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



Included Products

760049767 – TeraSPEED® ST Multiport Shuttered Adapter, Blue, Single Pack
SFA-ST06-BL-SHUTTERED

760049767 | SFA-ST06-BL-SHUTTERED



TeraSPEED® ST Multiport Shuttered Adapter, Blue, Single Pack

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber adapter |
| Product Brand | TeraSPEED® |
| Product Series | SFA |

General Specifications

| | |
|------------------------------|-----------|
| Body Style | Ganged |
| Color | Blue |
| Interface | ST/UPC |
| Mounting | No flange |
| Shuttered | Yes |
| Total Ports, quantity | 6 |

Material Specifications

| | |
|----------------------------------|----------|
| Alignment Sleeve Material | Zirconia |
|----------------------------------|----------|

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |

760049767 | SFA-ST06-BL-SHUTTERED

UK-ROHS

Compliant

