

TK-TW



Torque Wrench kit , includes tool bag and coupling torque wrench for N type and Din connectors

OBSOLETE

Product Classification

Product Type	Wrench
Ordering Note	CommScope® non-standard product

General Specifications

Application	Attaches connectors to coaxial cable
Calibration	6 mo
Tool Type	Torque wrench

Dimensions

Wrench Opening	20.574 mm 0.81 in 31.75 mm 1.25 in
-----------------------	--

Material Specifications

Material Type	Steel
----------------------	-------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

TK-TW

ROHS Compliant

UK-ROHS Compliant



Included Products

- 244377 – Torque Wrench for coupling torque of 7-16 DIN connectors, 1-1/4 in opening
- 244379 – Torque Wrench for coupling torque of Type N connectors, 13/16 in opening

244377

Torque Wrench for coupling torque of 7-16 DIN connectors, 1-1/4 in opening



Product Classification

Product Type	Wrench
Ordering Note	CommScope® standard product in Asia Pacific

General Specifications

Application	Torques DIN connectors
Calibration	6 mo
Tool Type	Torque wrench

Dimensions

Nominal Size	1-1/4 in 1-5/8 in 1/2 in 1/4 in 2-1/4 in 3/8 in 5/8 in 7/8 in
Wrench Opening	31.75 mm 1.25 in

Material Specifications

Material Type	Steel
----------------------	-------

Mechanical Specifications

Torque Tolerance	-0/+2
Torque Value	228 in lb 25.761 N-m

Packaging and Weights

Height, packed	381 mm 15 in
Width, packed	73.66 mm 2.9 in
Length, packed	73.66 mm 2.9 in
Packaging quantity	1
Weight, gross	0.89 kg 1.962 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system

244379

Torque Wrench for coupling torque of Type N connectors, 13/16 in opening



Product Classification

Product Type	Wrench
Ordering Note	CommScope® standard product in Asia Pacific

General Specifications

Application	Torques Type N connectors
Calibration	6 mo
Tool Type	Torque wrench

Dimensions

Nominal Size	1-1/4 in 1-5/8 in 1/2 in 1/4 in 2-1/4 in 3/8 in 5/8 in 7/8 in
Wrench Opening	20.574 mm 0.81 in

Material Specifications

Material Type	Steel
----------------------	-------

Mechanical Specifications

Torque Tolerance	-5/+0
Torque Value	20 in lb 2.26 N-m

Packaging and Weights

Height, packed	256.54 mm 10.1 in
Width, packed	88.9 mm 3.5 in
Length, packed	88.9 mm 3.5 in
Packaging quantity	1
Weight, gross	0.33 kg 0.728 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system