760239946XXXXXXXX | 18" Pole Base 4G/5G, Round

Round 18 inch diameter, Integrated Pole Base Concealment Pole for 4G /5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low to mid power 4G/5G outdoor small cell site
- Pole top concealment module for LAA/CBRS radio mounting
- Base of 18in diameter accepts low power radios or mid-power dual band radios
- Concealment integrates AC load load center/OVP and disconnect

Product Classification

Portfolio	CommScope®
Product Type	Integrated pole
Product Brand	Metro Cell
Warranty	One year

General Specifications

Antenna Compatibility, CommScope	CommScope Canister Antennas
Antenna Compatibility, Other Vendors	ACE | AMPHENOL | GALTRONICS | GAMMA NU | JMA | KATHREIN | KMW | ROSENBERGER
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) | Black | Black Green (RAL 6012) | Brown (RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Pure White | Umbra Grey (RAL 7022)
Cooling	Fan Cooling
Power Supply Compatibility	ABB CC1600 | DELTA 2.0 | PSU-AC-08
Radio Compatibility, Ericsson	(3) 2205/2208 (Pole Top) | (6) 2203/2205/2208 radios | 1281 | 220x | 440x | 4415 | 4426 | 4478 | 6701 | DELTA 2.0 | Diplexer | Power Distribution
Radio Compatibility, Nokia	(1) Airscale Dual Band 160W + (2) AirScale micro radios | (1) Airscale Dual Band 320W | (2) Airscale micro radios – LAA & CBRS (Pole Top) | (4) Airscale micro radios (Base) | AHFIA | Diplexer | Power Distribution
Radio Compatibility Samsung	AT1K01 | AT1K02 | DELTA 2.0 | Diplexer | Power Distribution | RF4402D-D1A | RT2201-46A | RT4401-48A
Radios Included	None

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 24, 2021

760239946XXXXXXXX | 18" Pole Base 4G/5G, Round

Dimensions

Height	3,048 mm | 120 in
Height Note	10 ft tall Equipment Base
Pole Height Options	10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft
Width	457.2 mm | 18 in
Depth	457.2 mm | 18 in
Depth Note	Round
Pole Diameter	203.2 mm | 8 in

Electrical Specifications

Power/Fiber Input	AC load center with OVP and disconnect

Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Steel

Environmental Specifications

Thermal Compliance	GR-487

* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
Pole Height Options	Overall AGL Standard Height

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 24, 2021