860660020 | Round Straight 10.75" Pole with Ladder Ht Ports

10.75" Diameter Pole with Ports for Enclosure Mounting at Ladder Height Access for Small Cell Equipment and Smart City Devices

Metal pole that supports a variety of installation methods such as poured concrete, embedded pole, pre-cast, and helical foundations with ports for Enclosure mounting at ladder height access

Configurable color and pole height

22' and 25' Poles do not have luminaire mounts

Foundation Kit Ordered Separately

Product Classification

PortfolioCommScope®Product TypeStandard polesProduct BrandMetro Cell

Ordering Note CommScope® standard product with terms

Warranty One year

General Specifications

Color Galvanized

Color Options Antique Bronze (SRSL 45893) | Beige-Grey (RAL 7006) | Black (RAL 9005) | Black Green

(RAL 6012) | Brown (RAL 8014) | Fairfax Brown (SW 2856) | Faux Concrete | Federal Park Brown | Green (RAL 6005) | Light Gray (RAL 7035) | Metallic Silver | Signal Black

(RAL 9004) | Umbra Grey (RAL 7022) | White (RAL 9010)

Compatible Foundation Type Embedded Pole | Embedded with Foam | Helical Anchor | Poured Concrete | Pre-Cast

Concrete | Split Helical Anchors

Compatible Smart Devices Cameras | Digital Signage | Emergency Call Station | Environmental

Monitoring | Security Lighting | WIFI

Dimensions

Pole Height Options 10.668 m | 35 ft | 11.278 m | 37 ft | 12.192 m | 40 ft | 12.497 m | 41 ft | 6.706

m | 22 ft | 7.62 m | 25 ft | 8.23 m | 27 ft | 8.534 m | 28 ft | 9.144 m | 30

ft | 9.754 m | 32 ft

Width 273.05 mm | 10.75 in

Luminaire Mount Height 7.315 m | 24 ft

Mounting Bolt Circle Diameter 406.4 mm | 16 in



860660020 | Round Straight 10.75" Pole with Ladder Ht Ports

Material Specifications

Finish Powder coated

Material Type Galvanized steel

Included Products

860644785-CK BASE COVER FOR COMMSCOPE 10" AND 860649813 POLES BASE COVER FOR COMMSCOPE 10" AND 860649813 POLES

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

Pole Height Options Overall AGL Standard Height

860644785-CK | BASE COVER FOR COMMSCOPE 10" AND 860649813 POLES



BASE COVER FOR COMMSCOPE 10" AND 860649813 POLES

Product Classification

Product Type Pole Accessory

Product Brand Metro Cell

Ordering Note CommScope® standard product with terms

Warranty One year

General Specifications

Color Light Gray (RAL 7035)

Color Options Antique Bronze (SRSL 45893) | Beige-Grey (RAL 7006) | Black (RAL 9005) | Black Green (RAL

6012) | Brown (RAL 8014) | Fairfax Brown (SW 2856) | Green (RAL 6005) | Light Gray (RAL 7035) | Metallic Silver | Signal Black (RAL 9004) | Umbra Grey (RAL 7022) | White (RAL

9010)

Dimensions

 Height
 155.702 mm | 6.13 in

 Width
 444.5 mm | 17.5 in

 Depth
 447.802 mm | 17.63 in

Material Specifications

Finish Powder coated
Finish Concealment Covers Powder coated
Material Type Aluminum

Packaging and Weights

Weight (unloaded) 4.536 kg | 10 lb

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

Page 3 of 4

860644785-CK | BASE COVER FOR COMMSCOPE 10" AND 860649813 POLES

