

REV	MCO	DWN	DATE
A	20245512	GTC	30-JUL-08
B	20246633	GTC	14-AUG-08

- 1/4-20 X 1.00 T-BOLT
- LARGE FLAT WASHER
- LARGE LOCK WASHER
- 1/4-20 NUT
- VINYL CAP

ON PANDUIT SIDE OF ADAPTER
PUSH TOOTHED TAB INTO SLOT

CONVERSION BRACKET
6" SHOWN FOR REFERENCE

6" ADC FIBER GUIDE
(SHOWN FOR REFERENCE)

THE T-BOLT IS DESIGNED TO FIT THROUGH THE SLOT IN THE CONVERSION BRACKET AND INTO THE CHANNEL ON THE SIDE OF THE ADC FIBER GUIDE. WHEN THE T-BOLT IS IN THE CHANNEL OF THE FIBER GUIDE TURN IT CLOCKWISE AND TIGHTEN THE NUT.

THE ADC FIBER GUIDE IS TO BE PLACED INSIDE OF THE SLOTTED TABS ON THE CONVERSION BRACKET. YOU WILL HAVE TO GENTLY SQUEEZE THE TOP TO THE FIBER GUIDE TO FIT IT INTO THE BRACKET.

NOTES:

1. THIS CONVERSION KIT INCLUDES THE FOLLOWING:
 - CONVERSION BRACKET (1)
 - 1/4-20 X 1.00 T-BOLT (4)
 - 1/4-20 X .750 CARRIAGE BOLT (2)
 - LARGE FLAT WASHER (6)
 - LARGE SPLIT LOCK WASHER (6)
 - 1/4-20 NUT (6)
 - VINYL CAP (6)

CATALOG #: FGS-ACC147 AND FGS-ACC153



INFORMATION ON THIS DOCUMENT IS PROPRIETARY TO ADC AND SHALL NOT BE USED, COPIED, REPRODUCED OR DISCLOSED IN WHOLE OR IN PART WITHOUT WRITTEN CONSENT OF ADC.		TITLE CONVERSION BRACKET KIT INSTALATION DRAWING	
ALL DIMS AND TOLERANCES ARE INCHES UNLESS OTHERWISE SPECIFIED	.XX:±N/A .XXX:±N/A ANGULAR:±N/A	C SIZE	DRAWING NUMBER 1449585
DO NOT SCALE DRAWING		ENGR: DEREK SAYRES DWN: GLEN CORDLE	B REV
		SHT. 1 OF 1	

**DIMENSIONS IN INCHES
THIRD ANGLE PROJECTION**