



The cabinet is designed to house rack mounted equipment. This includes DC power systems, Fiber storage/splice trays, cell site routers, batteries, and other rack mounted equipment. This cabinet provides mechanical and environmental protection for the equipment inside.

- Excellent Thermal Performance compatible with a DAC or HVAC
- Provides mounting space for power distribution, network servers, batteries, or other equipment.
- Front door compatible with Pad Lock.
- Provides flexible access for the cable entrances.
- Optional heater for cold environments.
- Provides 8RU of 19" Rack Space for Equipment
- Common parts available across the same platform.

Product Classification

Product Type Micro cell site enclosure

General Specifications

Alarm Type	Door open (both front and side doors) HVAC alarms (including high temperature, failure) S2 module, 20P or standard and user defined alarms
Batteries	Not included
Color	Gray
Cooling	Direct air cooling
Door Security	Quarter turn lock, puck lock system for rear door Swing handle, puck lock system for front door
Mounting	H-frame Pad Pole Universal wall mount
Noise Emission, maximum	65 dBA
Rack Type	EIA 19 in
Rack Units	8

Dimensions


Height	558.8 mm 22 in
Width	609.6 mm 24 in
Depth	558.8 mm 22 in

S8B0-D1-A00D00-01 | CMC8S

Electrical Specifications

Cooling Capacity	600 W
Voltage	-48 Vdc

Cabinet Dimensions and Door Clearances



Material Specifications

Finish	Powder coated
Material Type	Aluminum

Environmental Specifications

Operating Temperature	-40 °C to +46 °C (-40 °F to +115 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Qualification Standards	OSHA Telcordia GR-487
Thermal Compliance	GR-487

Packaging and Weights

Weight, net	34.019 kg 75 lb
--------------------	-------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system