## 5204203 | P3 750 JCASS SM PR997



# 75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground

 \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

### Product Classification

Regional Availability	North America
Product Type	Coaxial hardline cable
Product Brand	P3®
Government Requirements	Build America Buy America (BABA) compliant*
Warranty	One year
General Specifications	
Cable Type	750 Series
Construction Type	Swaged
Jacket Color	Black
Location of Manufacturing	Catawba, North Carolina
Short Description	P3 750 JCASS SM PR997
Dimensions	
Cable Length	762 m   2500 ft
Diameter Over Center Conductor, nominal	4.242 mm   0.167 in
Diameter Over Dielectric, nominal	17.323 mm   0.682 in
Diameter Over Jacket, nominal	21.082 mm   0.83 in
Diameter Over Outer Conductor, nominal	19.05 mm   0.75 in
Jacket Thickness, nominal	0.889 mm   0.035 in
Outer Conductor Thickness, nominal	0.864 mm   0.034 in

### **Electrical Specifications**

Capacitance

50.197 pF/m | 15.3 pF/ft

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 6, 2025



### 5204203 | P3 750 JCASS SM PR997

Capacitance Tolerance	±1.0 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±2 ohm
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	1.87 ohms/km   0.57 ohms/kft
dc Resistance, Loop, nominal	2.493 ohms/km   0.76 ohms/kft
dc Resistance, Outer Conductor, nominal	0.623 ohms/km   0.19 ohms/kft
Jacket Spark Test Voltage	5000 Vac
Nominal Velocity of Propagation (NVP)	87 %
Operating Frequency Band	5-3000 MHz
Structural Return Loss	24 dB @ 1003–1218 MHz   24 dB @ 1219–1794 MHz   30 dB @ 5–1002 MHz
Structural Return Loss, Grade N	≥24 dB @ 1003-1218 MHz   ≥24 dB @ 1219-1794 MHz   ≥30 dB @ 5-1002 MHz

### Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.36	0.11
55.0	1.21	0.37
85.0	1.51	0.46
204.0	2.36	0.72
211.0	2.43	0.74
250.0	2.66	0.81
300.0	2.92	0.89
350.0	3.18	0.97
400.0	3.44	1.05
450.0	3.67	1.12
500.0	3.87	1.18
550.0	4.07	1.24
600.0	4.3	1.31
750.0	4.86	1.48
865.0	5.28	1.61
1002.0	5.72	1.74
1218.0	6.41	1.95
1500.0	7.3	2.23

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 6, 2025



# 5204203 | P3 750 JCASS SM PR997

1794.0	8.07	2.46
1800.0	8.08	2.46
2000.0	8.57	2.61
2200.0	9.05	2.76
2500.0	9.73	2.96
2700.0	10.16	3.1
3000.0	10.8	3.29

### Material Specifications

Center Conductor Material	Copper-clad aluminum
Dielectric Material	Foam PE
Jacket Material	PE
Outer Conductor Material	Aluminum

### Mechanical Specifications

Minimum Bend Radius, bonded	152.4 mm   6 in
Pulling Tension, maximum	306.175 kg   675 lb

### **Environmental Specifications**

Corrosion Protection	Migraheal®
Environmental Space	Buried
Packaging and Weights	
Packaging Type	Reel

Weight, gross

398.828 kg/km | 268 lb/kft

### Regulatory Compliance/Certifications

CHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductCompliance	Agency	Classification
	CHINA-ROHS	Below maximum concentration value
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance	ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
	REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS Compliant	ROHS	Compliant
UK-ROHS Compliant	UK-ROHS	Compliant



Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 6, 2025

