


# 810010477/DB | D-012-DN-8G-M12BK/AY-0500-UK00

---



Optical Fiber OSP Drop cable, HDPE jacket, ST buffer, Singlemode, G.657. A2, 12 fiber, meter marked, black jacket color. Box Packaged in 500m lengths.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber drop cable
<b>Product Series</b>	D-DN


## General Specifications

<b>Cable Type</b>	Drop
<b>Construction Type</b>	Non-armored
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	12
<b>Buffer Type</b>	Micro-module
<b>Buffer Strip</b>	500 mm   19.685 in

## Dimensions

<b>Cable Length</b>	500 m   1,640.42 ft
<b>Buffer Tube/Subunit Diameter</b>	1.45 mm   0.057 in
<b>Diameter Over Jacket</b>	5 mm   0.197 in

## Representative Image



## Material Specifications

**Jacket Material** High density polyethylene (HDPE)

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	60 mm   2.362 in
<b>Minimum Bend Radius, unloaded</b>	30 mm   1.181 in
<b>Tensile Load, long term, maximum</b>	400 N   89.924 lbf
<b>Fiber Strain, long term, maximum</b>	0.33 %
<b>Tensile Load, short term, maximum</b>	800 N   179.847 lbf
<b>Fiber Strain, short term, maximum</b>	0.66 %
<b>Compression</b>	20 N/mm   114.203 lb/in
<b>Compression Test Method</b>	FOTP-41   IEC 60794-1 E3
<b>Flex</b>	100 cycles
<b>Flex Test Method</b>	FOTP-104   IEC 60794-1 E6
<b>Impact</b>	10 N-m   88.507 in lb
<b>Impact Test Method</b>	FOTP-25   IEC 60794-1 E4
<b>Strain Test Method</b>	FOTP-33   IEC 60794-1 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	FOTP-85   IEC 60794-1 E7

## Optical Specifications

**Fiber Type** G.657.A2

## Environmental Specifications

**Installation temperature** -10 °C to +60 °C (+14 °F to +140 °F)  
**Operating Temperature** -20 °C to +70 °C (-4 °F to +158 °F)  
**Storage Temperature** -20 °C to +70 °C (-4 °F to +158 °F)  
**Cable Qualification Standards** IEC 60794-1-2 | Telcordia GR-20  
**Environmental Space** Aerial, self-support | Buried | Drop | Façade | Underground (duct)  
**Jacket UV Resistance** UV stabilized  
**Water Penetration** 24 h  
**Water Penetration Test Method** FOTP-82 | IEC 60794-1 F5

## Environmental Test Specifications

**Cable Freeze Test Method** FOTP-98 | IEC 60794-1 F15  
**Heat Age** -20 °C to +85 °C (-4 °F to +185 °F)  
**Heat Age Test Method** IEC 60794-1 F9  
**Low High Bend** -10 °C to +60 °C (+14 °F to +140 °F)  
**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11  
**Temperature Cycle** -20 °C to +60 °C (-4 °F to +140 °F)  
**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

## Packaging and Weights

**Cable weight** 15 kg/km | 10.08 lb/kft

## Included Products

CS-8G-MP – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable