

# SSH-78-4

---

SnapStak® Hanger for 7/8 in coaxial cable, quadruple stack capability, includes reinforcement bar



## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	SnapStak®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Hanger Type</b>	Snap-in hanger
<b>Mounting</b>	3/4 in drilled cable ladder

## Dimensions

<b>Maximum Stack Height</b>	4
<b>Height</b>	40.9 mm   1.61 in
<b>Width</b>	40.1 mm   1.579 in
<b>Length</b>	64 mm   2.52 in
<b>Compatible Cable Diameter Range</b>	26.7–31 mm
<b>Compatible Diameter, maximum</b>	31 mm   1.22 in
<b>Compatible Diameter, minimum</b>	26.7 mm   1.051 in
<b>Nominal Size</b>	7/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

# SSH-78-4

---

**Material Type** Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Double cable weight

## Packaging and Weights

**Height, packed** 15.6 cm | 6.142 in

**Width, packed** 14.8 cm | 5.827 in

**Length, packed** 10.8 cm | 4.252 in

**Packaging quantity** 10

**Weight, gross** 0.42 kg | 0.926 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

## Included Products

SSHR-10 – SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power

# SSHR-10

---



SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

## Product Classification

<b>Product Type</b>	Adapter
<b>Product Brand</b>	SnapStak®
<b>Ordering Note</b>	CommScope® standard product in the United States and Canada

## General Specifications

<b>Accessories</b>	Adapters
<b>Color</b>	Black
<b>Mounting</b>	3/4 in through hole

## Dimensions

<b>Height</b>	76.2 mm   3 in
<b>Width</b>	25.4 mm   1 in
<b>Length</b>	6.35 mm   0.25 in

## Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

## Mechanical Specifications

<b>Maximum Loading</b>	Quadruple stack for SSH-M   Triple stack for hangers SSH-XL, SSH-L   Triple stack, 1-5/8 in cable
<b>Vibration Survival</b>	≥4 hours at resonant frequency

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours exposure in accelerated UV life chamber

## Packaging and Weights

<b>Height, packed</b>	17 cm   6.693 in
-----------------------	------------------

# SSHR-10

---

<b>Width, packed</b>	13 cm   5.118 in
<b>Length, packed</b>	10 cm   3.937 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.15 kg   0.331 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

