

IFEB

Base Product



IFEB Indoor Fiber Optic Wall mount Enclosure

- Compact, wall mountable fiber enclosures for indoor use
- Specifically designed for fast FTTH deployment and easy customer connection
- Configurable as splice only or connectorized solution
- Multiple and modular wrap around cable port sealing options to suit a wide range of cables
- Easy intergration of 900µm connectorised or 250µm splice splitters
- Single Element (SE), Single Slim Element (SLE) or Single Circuit (SC) tray options - Smouv and ANT
- Powered by NOVUX™

The Indoor Fiber Entrance Box is ideal for small to medium size buildings. It provides a flexible fiber management system for transitioning outside plant cable to indoor cable via splicing or with connectorized cable assemblies.

It incorporates proven fiber routing procedures, cable termination accessories and splice trays resulting in consistent, high-quality fiber management.

Product Classification


Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber wall box
Product Series	IFEB

General Specifications

Functionality	Patching Splicing
Access	Front
Enclosure Color	Pure White (RAL 9010)
Front Cover Type	Snap-on cover
Interface	LC/APC SC/APC SC/UPC Splicing only
Splicing Type	ANT SMOUV

Ordering Tree

IFEB



Environmental Specifications

Installation temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Indoor
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 60529, IP50 IEC 61753-1 Ed.2 2018 - Category C

Packaging and Weights

Packaging quantity	1
Packaging Type	Box