

# SRC3-U1B1B3BE000



NOVUX™ Specialty Range Closure 100, splice/patch, 2x SC/UPC adapter, No pigtail, 1:4 splitter, 12 splices, SMOUV® 45mm splice protectors, black, NO splitter, 2x NVX-CR-TI-SM-NN cable retention

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope’s Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

## Product Classification

Regional Availability	Asia   EMEA   Latin America   North America
Regional Availability Note	Contact your local CommScope representative for specific availability
Product Type	Access terminal, non-hardened
Product Brand	NOVUX™
Product Series	SRC100

## General Specifications

Cable Capacity, Drop	4 Flat 8.0 x 4.5 mm (0.30 x 0.17 in)   4 Round 1.2–8.0 mm (0.05–0.31 in)
Cable Sealing Type	Compressed gel
Enclosure Color	Black
Lock Type	Hinged with latches
Mounting	Handhole   Partially buried   Pedestal   Wall/Pole Mount, mounting kit included
Port Type	SC/UPC
Port, quantity	2
Splice Tray Included, quantity	1
Splice Tray Type Included	12-way, heat shrink
Splicing Capacity, maximum	12
Splicing Type, Supported	Single fusion
Splitter Type	1 x 4
Splitter, quantity	0

# SRC3-U1B1B3BE000

## Dimensions

Height	267 mm   10.512 in
Width	117 mm   4.606 in
Depth	49 mm   1.929 in

## Ordering Tree

SRC

-U

000

Size and color

3

100 Black

4

100 Gray

Sealing

U

Underground, IP68

Connector type\*

1

SC/UPC

2

LC/UPC

3

SC/APC

4

LC/APC

5

Splice only

\*All connector types are grade B

Number of adapters

A

None

K

1

B

2

Cable retention

\* See complete details at the bottom of the page.

Splice protector type

A

ANT/SMOUV 30

B

SMOUV 45

F

Ribbon 12

Splitters

1

None

2

1:2

3

1:4

Number of splices

B

12

C

24

D

48

Number of pigtails

1

None

A

1

2

2

B

3

3

4

2 cable attachments are supplied.

Cable retention\*

A

None

B

NVX-CR-MC-FT-NN

C

NVX-CR-MC-RD-NN

D

NVX-CR-SA-SM-NN

E

NVX-CR-TI-SM-NN

F

NVX-CR-DU-FL-NN

G

4xNVX-CR-MC-FT-NN

H

4xNVX-CR-MC-RD-NN

I

4xNVX-CR-SA-SM-NN

J

4xNVX-CR-TI-SM-NN

K


4xNVX-CR-DU-FL-NN

L

2xNVX-CR-MC-FT-NN and 2xNVX-CR-MC-RD-NN

Cable Termination Unit (CTU) options


B



NVX-CR-MC-FT-NN

- Flat cable
- Metal clip
- Range 3 x 5 to 4 x 8 mm


C



NVX-CR-MC-RD-NN

- Round cable
- Metal clip
- Range 4 to 6.2 mm


D



NVX-CR-SA-SM-NN

- Round cable
- Dia up to 8 mm
- Strength member
- Aramid yarns
- Single layer


E



NVX-CR-TI-SM-NN

- Round cable
- Dia up to 8 mm
- Aramid yarns
- Single layer

F



NVX-CR-DU-FL-NN

- Round cable
- Dia up to 6.2 mm
- Aramid yarns
- Dual layer
- Compact length

## Material Specifications

Enclosure Material Type	Impact-resistant polymer
-------------------------	--------------------------

## Optical Specifications

Fiber Type	G.657.A1   G.657.A2   G.657.B3
------------	--------------------------------

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see <https://www.commscope.com/trademarks>. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 27, 2025

COMMScope®

# SRC3-U1B1B3BE000

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Environmental Space</b>	Above ground   Below ground   Direct burial
<b>Qualification Standards</b>	IEC 60529, IP68 + 2 m waterhead   IEC 61753-1, category G
<b>UV Resistance</b>	UV stabilized

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton

## Included Products

NVX-CR-TI-SM-NN	–	NOVUX™ Cable Termination Unit (CTU) for round cables up to 8 mm diameter, with aramide yarns, single layer
-----------------	---	--