

GigaSPEED X10D® 2091SDB ETL verified Category 6A U/UTP Cable, plenum, orange jacket, 4 pair count, 3000 ft (915 m) length, reel

- Part of the SYSTIMAX GigaSPEED X10D family of products
- Meets and exceeds performance specifications for all channel configurations currently supported by the GigaSPEED X10D system

## Product Classification

Regional Availability	Latin America   North America
Portfolio	SYSTIMAX®
Product Type	Twisted pair cable
Product Brand	GigaSPEED X10D®


## General Specifications

Product Number	2091SDB
ANSI/TIA Category	6A
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	Orange
Note	Consult ANSI/TIA-568-C.2 Annex G for length de-rating guidance for cable installation in higher temperature environments
Pairs, quantity	4
Separator Type	Isolator
Transmission Standards	ANSI/TIA-568.2-D

## Dimensions

Cable Length	914.4 m   3000 ft
Diameter Over Insulated Conductor	1.115 mm   0.044 in
Diameter Over Jacket, nominal	6.325 mm   0.249 in
Jacket Thickness	0.406 mm   0.016 in
Conductor Gauge, singles	23 AWG

### Cross Section Drawing



### Electrical Specifications

dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	8 ohms/100 m   2.438 ohms/100 ft
Dielectric Strength, minimum	1500 Vac   2500 Vdc
LP (Limited Power) Rating	0.7 A
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	70 %
Operating Frequency, maximum	500 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

### Material Specifications

Conductor Material	Bare copper
Insulation Material	FEP
Jacket Material	PVC
Separator Material	FEP
Tape Material	Poly/Aluminum/Poly

### Mechanical Specifications

Pulling Tension, maximum	11.34 kg   25 lb
--------------------------	------------------

Environmental Specifications

Installation temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +75 °C (-4 °F to +167 °F)
Environmental Space	Plenum
Temperature Rating, UL	105 °C   221 °F
Flame Test Method	CMP/FT6
Smoke Test Method	CMP/FT6

Packaging and Weights

Cable weight	58.038 kg/km   39 lb/kft
Packaging Type	Reel