6-57826-4 | CS24R GRY C5E 4/24 U/UTP CPK 1KFT

Copper Cable, category 5e, 4 pair, UTP, 350 MHz, CMR rated, 1000 ft pull-box, gray



Regional Availability	Asia
Portfolio	NETCONNECT®
Product Type	Twisted pair cable
Product Series	520 Series
General Specifications	
Product Number	520R
ANSI/TIA Category	5е
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	Gray
Pairs, quantity	4
Transmission Standards	ANSI/TIA-568.2-D CENELEC EN 50288-6-1 ISO/IEC 11801 Class D
Dimensions	
Cable Length	304.8 m 1000 ft
Diameter Over Jacket, nominal	4.699 mm 0.185 in
Conductor Gauge, singles	24 AWG
Electrical Specifications	
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1,

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 11, 2024



6-57826-4 | CS24R GRY C5E 4/24 U/UTP CPK 1KFT

CENELEC EN 50174-2 or TIA TSB-184-A

Safety Voltage Rating

300 V

Electrical Cable Performance

CS	CommScope				
STD	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above				
ТҮР	Typical Electrical Performance				
IL	Insertion Loss (dB/100m)	NEXT	Near End Crosstalk (dB/100m)		
ACR	Attenuation to Crosstalk Ratio (dB/100m)	PSNEXT	Power Sum Near End Crosstalk (db/100m)		
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)		
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)	RL	Return Loss (dB)		
TCL	Transverse Conversion Loss (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)		

Freq.	L	NEXT	ACR	PSNEXT	PSACR	ACRF	PSACRF	RL
MHz	STD	STD	STD	STD	STD	STD	STD	STD
1	2	65.3	63.3	62.3	60.3	63.8	60.8	20
4	4.1	56.3	52.2	53.3	49.2	51.8	48.8	23
8	5.8	51.8	46	48.8	43	45.7	42.7	24.5
10	6.5	50.3	43.8	47.3	40.8	43.8	40.8	25
16	8.2	47.2	39	44.2	36	39.7	36.7	25
20	9.3	45.8	36.5	42.8	33.5	37.8	34.8	25
25	10.4	44.3	33.9	41.3	30.9	35.8	32.8	24.3
31.25	11.7	42.9	31.2	39.9	28.2	33.9	30.9	23.6
62.5	17	38.4	21.4	35.4	18.4	27.9	24.9	21.5
100	22	35.3	13.3	32.3	10.3	23.8	20.8	20.1

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	PVC

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Non-plenum

Packaging and Weights

Cable weight	32.74 kg/km	22 lb/kft

Packaging Type

Regulatory Compliance/Certifications

Agency

Classification

Pull box

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 11, 2024



CS24R GRY C5E 4/24 U/UTP CPK 1KFT 6-57826-4

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS



Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 11, 2024

