222040-2

EWP90S, HELIAX® Super Premium Elliptical Waveguide, 10.7–11.7 GHz, unjacketed

Product Classification

Product Type Elliptical waveguide

Product Brand HELIAX®

General Specifications

Performance Note Values typical, unless otherwise stated

Dimensions

Diameter Over Jacket (E Plane)33.5 mm1.319 inDiameter Over Jacket (H Plane)20.3 mm0.799 in

Cable Volume 334 L/km | 3.595 ft³/kft

Electrical Specifications

eTE11 Mode Cutoff 6.5 GHz

Group Delay at Frequency 125 ns/100 ft @ 11.200 GHz | 410 ns/100 m @ 11.200 GHz

Operating Frequency Band 10.7 – 11.7 GHz

VSWR/Return Loss

 Frequency Band
 VSWR
 Return Loss (dB)

 10.7–11.7 GHz
 1.05
 32.3

Attenuation

Frequency (GHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)	Group Velocity %
10.7	10.311	3.143	1.559	79.4
10.9	10.198	3.108	1.576	80.3
11.1	10.096	3.077	1.592	81.1
11.3	10.004	3.049	1.606	81.8
11.5	9.92	3.024	1.62	82.5
11.7	9.843	3	1.633	83.1

Material Specifications

Conductor Material Corrugated copper

Jacket Material Unjacketed

Page 1 of 2

222040-2

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)180 mm | 7.087 inMinimum Bend Radius, Multiple Bends (H Plane)480 mm | 18.898 inMinimum Bend Radius, Single Bend (E Plane)150 mm | 5.906 inMinimum Bend Radius, Single Bend (H Plane)330 mm | 12.992 inMaximum Twist6.562 °/m | 2 °/ft

Environmental Specifications

Installation temperature $-40 \, ^{\circ}\text{C}$ to $+60 \, ^{\circ}\text{C}$ ($-40 \, ^{\circ}\text{F}$ to $+140 \, ^{\circ}\text{F}$)Operating Temperature $-55 \, ^{\circ}\text{C}$ to $+85 \, ^{\circ}\text{C}$ ($-67 \, ^{\circ}\text{F}$ to $+185 \, ^{\circ}\text{F}$)Storage Temperature $-70 \, ^{\circ}\text{C}$ to $+85 \, ^{\circ}\text{C}$ ($-94 \, ^{\circ}\text{F}$ to $+185 \, ^{\circ}\text{F}$)

Attenuation, Ambient Temperature $75 \,^{\circ}\text{F}$ | $23.889 \,^{\circ}\text{C}$ Average Power, Ambient Temperature $104 \,^{\circ}\text{F}$ | $40 \,^{\circ}\text{C}$ Average Power, Temperature Rise $42 \,^{\circ}\text{C}$ | $107.6 \,^{\circ}\text{F}$

Packaging and Weights

Cable weight 0.48 kg/m | 0.323 lb/ft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

