


## Plenum MPO Trunk Cable, 24 fiber



### Product Classification

|                              |  |
|------------------------------|--|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America |
| <b>Portfolio</b>             | CommScope®   |
| <b>Product Type</b>          | Fiber indoor cable   |
| <b>Product Series</b>        | P-MP   |


### General Specifications

|                                     |                 |
|-------------------------------------|-----------------|
| <b>Cable Type</b>                   | MPO trunk cable |
| <b>Construction Type</b>            | Non-armored     |
| <b>Subunit Type</b>                 | Gel-free        |
| <b>Jacket Color</b>                 | Yellow          |
| <b>Jacket Marking</b>               | Feet            |
| <b>Subunit, quantity</b>            | 1               |
| <b>Fibers per Subunit, quantity</b> | 24              |
| <b>Total Fiber Count</b>            | 24              |

### Dimensions

|                                     |                    |
|-------------------------------------|--------------------|
| <b>Buffer Tube/Subunit Diameter</b> | 3.6 mm   0.142 in  |
| <b>Diameter Over Jacket</b>         | 5.46 mm   0.215 in |

### Representative Image



## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 82 mm   3.228 in                      |
| <b>Minimum Bend Radius, unloaded</b>     | 55 mm   2.165 in                      |
| <b>Tensile Load, long term, maximum</b>  | 200 N   44.962 lbf                    |
| <b>Tensile Load, short term, maximum</b> | 667 N   149.948 lbf                   |
| <b>Compression</b>                       | 10 N/mm   57.101 lb/in                |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 300 cycles                            |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 0.74 N-m   6.55 in lb                 |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 500 m   1,640.42 ft                   |

## Optical Specifications

|                   |                           |
|-------------------|---------------------------|
| <b>Fiber Type</b> | G.657.A2/B2   G.657.A2/B2 |
|-------------------|---------------------------|

## Environmental Specifications

|                                 |                                    |
|---------------------------------|------------------------------------|
| <b>Installation temperature</b> | 0 °C to +70 °C (+32 °F to +158 °F) |
|---------------------------------|------------------------------------|

# 760238982 | P-024-MP-8G-F24YL

|                                      |                                       |
|--------------------------------------|---------------------------------------|
| <b>Operating Temperature</b>         | 0 °C to +70 °C (+32 °F to +158 °F)    |
| <b>Storage Temperature</b>           | -40 °C to +70 °C (-40 °F to +158 °F)  |
| <b>Cable Qualification Standards</b> | ANSI/ICEA S-83-596   Telcordia GR-409 |
| <b>Environmental Space</b>           | Plenum                                |
| <b>Flame Test Listing</b>            | NEC OFNP (ETL) and c(ETL)             |
| <b>Flame Test Method</b>             | NFPA 130   NFPA 262                   |

## Environmental Test Specifications

|                                      |                                    |
|--------------------------------------|------------------------------------|
| <b>Heat Age</b>                      | 0 °C to +85 °C (+32 °F to +185 °F) |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                     |
| <b>Low High Bend</b>                 | 0 °C to +70 °C (+32 °F to +158 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11          |
| <b>Temperature Cycle</b>             | 0 °C to +70 °C (+32 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1            |

## Packaging and Weights

|                     |                          |
|---------------------|--------------------------|
| <b>Cable weight</b> | 29 kg/km   19.487 lb/kft |
|---------------------|--------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable