75 Ohm P3® Trunk and Distribution Cable, black flame retardant PE jacket



 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America	
Product Type	Coaxial hardline cable	
Product Brand	P3®	
Government Funding	Build America Buy America (BABA) compliant*	
Warranty	One year	
General Specifications		
Cable Type	625 Series	
Construction Type	Swaged	
Jacket Color	Black	
Short Description	P3 625 JCAR SM PR8067	
Dimensions		
Cable Length	731.52 m 2400 ft	
Diameter Over Center Conductor, nominal	3.48 mm 0.137 in	
Diameter Over Dielectric, nominal	14.351 mm 0.565 in	
Diameter Over Jacket, nominal	17.399 mm 0.685 in	
Diameter Over Outer Conductor, nominal	15.875 mm 0.625 in	
Jacket Thickness, nominal	0.762 mm 0.03 in	
Outer Conductor Thickness, nominal	0.762 mm 0.03 in	
Electrical Specifications		
Capacitance	50.197 pF/m 15.3 pF/ft	

Capacitance Tolerance

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 11, 2024

±1.0 pF/ft



5447303 | P3® 625 JCAR

Characteristic Impedance	75 ohm	
Characteristic Impedance Tolerance	±2 ohm	
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)	
dc Resistance, Inner Conductor, nominal	2.756 ohms/km 0.84 ohms/kft	
dc Resistance, Loop, nominal	3.609 ohms/km 1.1 ohms/kft	
dc Resistance, Outer Conductor, nominal	0.853 ohms/km 0.26 ohms/kft	
Jacket Spark Test Voltage	5000 Vac	
Nominal Velocity of Propagation (NVP)	87 %	
Operating Frequency Band	5-3000 MHz	
Structural Return Loss	24 dB @ 1003–1218 MHz 24 dB @ 1219–1794 MHz 30 dB @ 5–1002 MHz	
Structural Return Loss, Grade N	≥24 dB @ 1003-1218 MHz ≥24 dB @ 1219-1794 MHz ≥30 dB @ 5-1002 MHz	

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.43	0.13
55.0	1.48	0.45
85.0	1.84	0.56
204.0	2.92	0.89
211.0	3.02	0.92
250.0	3.28	1
300.0	3.54	1.08
350.0	3.87	1.18
400.0	4.17	1.27
450.0	4.43	1.35
500.0	4.69	1.43
550.0	4.92	1.5
600.0	5.18	1.58
750.0	5.84	1.78
865.0	6.33	1.93
1002.0	6.92	2.11
1218.0	7.62	2.32
1500.0	8.74	2.66
1794.0	9.7	2.96

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 11, 2024



5447303 | P3® 625 JCAR

1800.0	9.72	2.96
2000.0	10.34	3.15
2200.0	10.95	3.34
2500.0	11.81	3.6
2700.0	12.37	3.77
3000.0	13.19	4.02

Material Specifications

um

Mechanical Specifications

Minimum Bend Radius, bonded	114.3 mm 4.5 in
Pulling Tension, maximum	215.456 kg 475 lb

Environmental Specifications

Environmental Space	Riser
Temperature Rating, UL	60 °C 140 °F
Flame Test Listing	CATVR NEC Article 820

Packaging and Weights

Packaging Type Weight, gross Reel 296.145 kg/km | 199 lb/kft

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification Designed, manufactured and/or distributed under this quality management system



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 11, 2024

