

RCT4-WBC-1X-RNA



RCT4, RADIAX® Coaxial Radiating Cable with Bump, 50–3800 MHz, foil, 1/2 in, black non-halogenated, fire retardant polyolefin jacket

Product Classification

Product Type	Radiating cable
Product Brand	RADIAX®
Product Series	RCT4

General Specifications

Polarization	Vertical
Cable Type	Coupled Mode Series
Jacket Color	Black

Dimensions

Diameter Over Jacket, maximum	16.256 mm 0.64 in
Inner Conductor OD	4.826 mm 0.19 in
Outer Conductor OD	12.954 mm 0.51 in
Nominal Size	1/2 in
Recommended Distance from the Wall	50.8 mm 2 in
Recommended Hanger Spacing	1 m 3.281 ft

Electrical Specifications

Attenuation Test Method	IEC 61196-4
Attenuation Tolerance	±5%
Cable Impedance	50 ohm ±3 ohm
dc Resistance, Inner Conductor	1.48 ohms/km 0.451 ohms/kft
dc Resistance, Outer Conductor	5.305 ohms/km 1.617 ohms/kft
dc Test Voltage	4000 V
Insulation Resistance	100000 Mohms•km

RCT4-WBC-1X-RNA

Jacket Spark Test Voltage (rms)	8000 V
Operating Frequency Band	50 – 3800 MHz
Peak Power	40 kW
Velocity	88 %
VSWR Installed, typical, 1700–2700 MHz	1.38
VSWR Installed, typical, 50–960 MHz	1.3
VSWR on Reel, typical	1.43

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Coupling Loss 50%	Coupling Loss 95%
75.0	1.8	0.54	59	67
100.0	2.1	0.65	52	63
150.0	2.6	0.79	61	71
350.0	3.9	1.19	72	83
450.0	4.4	1.34	74	84
700.0	6.4	1.95	73	83
800.0	6.9	2.1	73	84
900.0	7.4	2.3	73	85
960.0	7.7	2.4	73	85
1700.0	10.7	3.3	70	81
1800.0	11.2	3.4	69	80
1900.0	11.5	3.5	71	82
2000.0	11.6	3.6	69	81
2100.0	12.3	3.7	72	84
2200.0	12.5	3.8	70	82
2300.0	13.3	4.1	64	75
2400.0	13.8	4.2	66	77
2500.0	14.3	4.4	66	77
2600.0	14.7	4.5	65	75
2700.0	15.4	4.7	63	75
2800.0	16	4.9	60	70
3300.0	18.2	5.5	56	65
3400.0	18.6	5.7	56	65
3500.0	19.1	5.8	56	65

RCT4-WBC-1X-RNA

3600.0	20.8	6.33	58	65
3700.0	21.4	6.52	60	65
3800.0	22.2	6.76	61	67

Material Specifications

Dielectric Material	Foam PE
Jacket Material	Non-halogenated, fire retardant polyolefin
Inner Conductor Material	Copper-clad aluminum wire
Outer Conductor Material	Copper foil

Mechanical Specifications

Minimum Bend Radius, single Bend	127 mm 5 in
Tensile Strength	45 kg 99.208 lb
Bending Moment	3.7 N-m 32.748 in lb
Coupling Loss Test Method	IEC 61196-4
Coupling Loss Tolerance	±10 dB
Flat Plate Crush Strength	0.7 kg/mm 39.198 lb/in
Indication of Slot Alignment	Yes—bumps face the wall

Environmental Specifications

Installation temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-30 °C to +80 °C (-22 °F to +176 °F)
Storage Temperature	-30 °C to +80 °C (-22 °F to +176 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C
Fire Retardancy Test Method	IEC 60332-1 IEC 60332-3C-24
Smoke Index Test Method	IEC 61034
Toxicity Index Test Method	IEC 60754-1 IEC 60754-2

Packaging and Weights

Cable weight	0.19 kg/m 0.128 lb/ft
---------------------	-------------------------

Regulatory Compliance/Certifications

RCT4-WBC-1X-RNA

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

