RCT7-CPUS-4A-RNAM

RCT7, RADIAX® Coaxial Radiating Cable with Bump, 50–2400 MHz, tuned foil, 1-5/8 in, black non-halogenated, fire retardant polyolefin jacket

Product Classification

Product Type Radiating cable

Product Brand RADIAX®
Product Series RCT7

General Specifications

Polarization Vertical

 Cable Type
 Radiating Mode (RCT) Series

Jacket Color Black
Tape Barrier Mica

Dimensions

Diameter Over Jacket, maximum49.784 mm | 1.96 inInner Conductor OD18.161 mm | 0.715 inOuter Conductor OD43.815 mm | 1.725 in

Nominal Size 1-5/8 in

Recommended Distance from the Wall 101.6 mm | 4 in Recommended Hanger Spacing 1.3 m | 4.265 ft

Electrical Specifications

Attenuation Test Method IEC 61196-4

Attenuation Tolerance ±5%

Cable Impedance50 ohm ±2 ohm

dc Resistance, Inner Conductor1.435 ohms/km0.437 ohms/kftdc Resistance, Outer Conductor1.969 ohms/km0.6 ohms/kft

COMMSCOPE®

RCT7-CPUS-4A-RNAM

dc Test Voltage 15000 V

Insulation Resistance 100000 MOhms-km

Jacket Spark Test Voltage (rms) 10000 V

Operating Frequency Band 50 – 2400 MHz

Optimum Operating Frequency Band 1700 – 2400 MHz | 800 – 960 MHz

Peak Power 302 kW

Stop Bands 1110 – 1650 MHz

Velocity 93 %
VSWR Installed, typical, 1700–2700 MHz 1.38
VSWR Installed, typical, 50–960 MHz 1.3
VSWR on Reel, typical 1.43

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Coupling Loss 50%	Coupling Loss 95%
75.0	0.5	0.15	65	75
100.0	0.6	0.18	68	77
150.0	0.8	0.24	77	86
350.0	1.2	0.36	89	99
450.0	1.4	0.43	86	98
700.0	1.7	0.52	83	93
800.0	1.9	0.58	65	69
900.0	2.2	0.67	63	66
1700.0	5.2	1.59	54	58
1800.0	4.8	1.46	55	59
1900.0	4.7	1.43	56	61
2000.0	4.5	1.37	57	61
2100.0	4.5	1.37	59	63
2200.0	4.5	1.37	60	65
2300.0	4.5	1.37	60	66
2400.0	4.6	1.4	60	67

Material Specifications

Dielectric Material Foam PE

Jacket Material Non-halogenated, fire retardant polyolefin

Inner Conductor Material Corrugated copper tube

Page 2 of 3



RCT7-CPUS-4A-RNAM

Outer Conductor Material Copper foil

Mechanical Specifications

Minimum Bend Radius, single Bend 508 mm | 20 in

Tensile Strength 215 kg | 473.993 lb

Bending Moment 16 N-m | 141.612 in lb

Coupling Loss Test Method IEC 61196-4

Coupling Loss Tolerance ±5 dB

Flat Plate Crush Strength 0.8 kg/mm | 44.798 lb/in Indication of Slot Alignment Yes-bumps face the wall

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-30 \,^{\circ}\text{C} \text{ to } +80 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +176 \,^{\circ}\text{F})$

Storage Temperature $-30 \,^{\circ}\text{C}$ to $+80 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature $68~^{\circ}\text{F}~\mid~20~^{\circ}\text{C}$

Average Power, Ambient Temperature 104 $^{\circ}\text{F}$ | 40 $^{\circ}\text{C}$

Average Power, Inner Conductor Temperature 212 °F | 100 °C

Fire Retardancy Test Method IEC 60332-1-2 | IEC 60332-3C-24

Smoke Index Test Method IEC 61034

Toxicity Index Test Method IEC 60754-1 | IEC 60754-2

Packaging and Weights

Cable weight 0.83 kg/m | 0.558 lb/ft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



