5508002 | QR® 540 JCAT B

75 Ohm QR® Trunk and Distribution Cable, black PE jacket with coextruded blue stripe



*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability North America

Product Type Coaxial hardline cable

Product Brand QR®

Government FundingBuild America Buy America (BABA) compliant*

General Specifications

Cable Type540 SeriesConstruction TypeWelded

Jacket ColorBlack with co-extruded blue stripe

Short Description QR 540 JCAT B SM PR2171

Dimensions

Cable Length1,127.76 m | 3700 ftDiameter Over Center Conductor, nominal3.15 mm | 0.124 inDiameter Over Dielectric, nominal13.056 mm | 0.514 inDiameter Over Jacket, nominal15.494 mm | 0.61 inDiameter Over Outer Conductor, nominal13.716 mm | 0.54 inJacket Thickness, nominal0.889 mm | 0.035 inOuter Conductor Thickness, nominal0.343 mm | 0.014 in

Electrical Specifications

Capacitance 50.197 pF/m | 15.3 pF/ft



5508002 | QR® 540 JCAT B

Characteristic Impedance Tolerance ±2 ohm

dc Resistance Note

Nominal values based on a standard condition of 20 °C (68 °F)

dc Resistance, Inner Conductor, nominal3.346 ohms/km | 1.02 ohms/kftdc Resistance, Loop, nominal5.282 ohms/km | 1.61 ohms/kftdc Resistance, Outer Conductor, nominal1.936 ohms/km | 0.59 ohms/kft

Jacket Spark Test Voltage5000 VacNominal Velocity of Propagation (NVP)88 %

Operating Frequency Band 5-3000 MHz

Structural Return Loss 24 dB @ 1003-1218 MHz | 24 dB @ 1219-1794 MHz | 30 dB @ 5-1002

MHz

Structural Return Loss, Grade N ≥24 dB @ 1003−1218 MHz | ≥24 dB @ 1219−1794 MHz | ≥30 dB @ 5−1002

ИHZ

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.46	0.14
55.0	1.54	0.47
85.0	1.94	0.59
204.0	3.05	0.93
211.0	3.12	0.95
250.0	3.38	1.03
300.0	3.71	1.13
350.0	4.04	1.23
400.0	4.33	1.32
450.0	4.59	1.4
500.0	4.89	1.49
550.0	5.12	1.56
600.0	5.38	1.64
750.0	6.07	1.85
865.0	6.56	2
1002.0	7.12	2.17
1218.0	7.89	2.41
1500.0	9.07	2.76
1794.0	10.11	3.08
1800.0	10.13	3.09



5508002 | QR® 540 JCAT B

2000.0	10.81	3.29
2200.0	11.46	3.49
2500.0	12.41	3.78
2700.0	13.03	3.97
3000.0	13.93	4.24

Material Specifications

Center Conductor Material Copper-clad aluminum

Dielectric Material Foam PE

Jacket Material PE

Outer Conductor Material Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded101.6 mm | 4 inPulling Tension, maximum99.79 kg | 220 lb

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging Type Reel

Weight, gross 178.58 kg/km | 120 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

