


# 2-599619-3 | C-024-LN-5L-M12AQ/28D/E



Fiber Indoor/Outdoor Cable, 24-fiber, multimode OM3, gel-free, aqua jacket color, Eca Flame Rating, Meters jacket marking, 2000 meters

## OBSOLETE

This product was discontinued on: March 31, 2023

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-LN


## General Specifications

<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-free
<b>Filler, quantity</b>	2
<b>Jacket Color</b>	Aqua
<b>Jacket Marking</b>	Meters
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	24

## Dimensions

<b>Cable Length</b>	2000 m   6,561.68 ft
<b>Diameter Over Jacket</b>	11.5 mm   0.453 in

## Representative Image



## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	231.1 mm   9.098 in
<b>Minimum Bend Radius, unloaded</b>	170.2 mm   6.701 in
<b>Tensile Load, long term, maximum</b>	1201 N   269.996 lbf
<b>Tensile Load, short term, maximum</b>	2002 N   450.068 lbf

## Optical Specifications

**Fiber Type** OM3

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	1.00 dB/km @ 1,300 nm   3.50 dB/km @ 850 nm
<b>Standards Compliance</b>	IEC 60794-1   TIA-492AAAC (OM3)

## Environmental Specifications

<b>Installation temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Operating Temperature</b>	-10 °C to +70 °C (+14 °F to +158 °F)
<b>Storage Temperature</b>	-10 °C to +70 °C (+14 °F to +158 °F)
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Eca
<b>Environmental Space</b>	Universal Low Smoke Zero Halogen (ULSZH)

## Packaging and Weights

<b>Cable weight</b>	119 kg/km   79.964 lb/kft
---------------------	---------------------------

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable