

6-1553346-4

Indoor/Outdoor Fiber Optic Cable, Dry, 12-fiber, OFNR, OM3, black

OBSOLETE

This product was discontinued on: July 11, 2018

Product Classification

Regional Availability	Asia Latin America North America
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-DS

General Specifications

Cable Type	Loose tube
Fibers per Subunit, quantity	12
Jacket Color	Black
Jacket Marking	Meters
Subunit Type	Gel-free
Total Fiber Count	12

Dimensions

Diameter Over Jacket	7.3 mm 0.287 in
-----------------------------	-------------------

Mechanical Specifications

Minimum Bend Radius, loaded	152.4 mm 6 in
Minimum Bend Radius, unloaded	75 mm 2.953 in
Tensile Load, long term, maximum	400 N 89.924 lbf
Tensile Load, short term, maximum	1334 N 299.895 lbf

Optical Specifications

Fiber Type	OM3
-------------------	-----

Optical Specifications, Wavelength Specific

10 Gbps Ethernet Distance	300 m @ 850 nm
----------------------------------	----------------

6-1553346-4

Attenuation, maximum	1.00 dB/km @ 1,300 nm 3.20 dB/km @ 850 nm
Bandwidth, Laser, minimum	2,000 MHz-km @ 850 nm
Bandwidth, OFL, minimum	1,500 MHz-km @ 850 nm 500 MHz-km @ 1,300 nm
Standards Compliance	ANSI/TIA-568.B.1 ANSI/TIA-568.B.2 IEC 60793-2-10 TIA-492AAAC (OM3)

Environmental Specifications

Installation temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Riser

Packaging and Weights

Cable weight	53 kg/km 35.614 lb/kft
---------------------	--------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable