# CS3840-000 | FOSC-400BG-NT-0-NN



FOSC® 400 BG Fiber Optic Splice Closure, Gel Cable sealing, no pre-installed trays

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

#### **Product Classification**

Regional Availability Asia | EMEA

**Product Type** Single-ended, round fiber closure

Product Brand FOSC®

Product Series FOSC 400G

#### General Specifications

Cable Entry Drop Port StyleRoundCable Entry Main Port StyleRound

Cable Ports Quantity, total 1 oval port (2 cables) + 2 round ports

Cable Sealing TypeCompressed gel

Closure Sealing Type Dome-to-base clamp with O-ring

Closure Style Single-ended

**Color** Black

Mounting Pole | Strand | Wall

Network Area Type Feeder
Splice Tray Included, quantity 0

**Splicing Type, Supported** Single fusion


Dimensions

Main Cable Diameter, maximum 25 mm | 0.984 in

Ordering Tree



## CS3840-000 | FOSC-400BG-NT-0-NN



### Material Specifications

Material Type Impact-resistant polymer

### **Environmental Specifications**

Environmental Space Below ground | Buried

Packaging and Weights

Packaging quantity

Packaging TypeBox | CartonWeight, net2.3 kg | 5.071 lb

Regulatory Compliance/Certifications

**COMMSCOPE®** 

## CS3840-000 | FOSC-400BG-NT-0-NN

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

