CX1638-000 | FIST-GC0G2-DD6-NN



FIST® GCOG2 Fiber Optic Splice Closure, Gel Cable sealing, size DD, no pre-installed fiber trays, 6 ports

- Single-ended closure design where base and dome are sealed with a clamp and 0-ring system
- Includes FIST management system for fiber organization and splicing
- Uncut fibers can be stored as single circuits in trays and/or as cable elements in storage space between profiles
- Includes 6 round cable ports in a wrap-around block with pre-installed gel profile for cable sealing
- Universal mounting system (UMS) profiles provide foundation for mounting combinations of FIST splice trays
- Compatible with most common cable types: loose tube, central core, slotted core
- Storage baskets available for mass storage of fibers of central core cable constructions

Product Classification

Regional Availability EMEA

Product Type Single-ended, round fiber closure

Product Brand FIST®

Product Series FIST-GC0G2

General Specifications

Cable Entry Drop Port StyleRoundCable Entry Main Port StyleOval

Cable Ports Quantity, total6 round portsCable Sealing TypeCompressed gel

Closure Sealing Type Dome-to-base clamp with O-ring

Closure Style Single-ended

Color Black
Flash Test Valve None
Ground Feed-through None

Mounting Pole | Strand | Wall

Network Area Type Distribution

Splice Tray Included, quantity 0

Splice Tray Type Included No trays

Splicing Type, Supported Mass fusion | Single fusion



CX1638-000 | FIST-GCOG2-DD6-NN

Dimensions


 Length
 645 mm | 25.394 in

 Diameter
 247 mm | 9.724 in

 Diameter, with clamp
 291 mm | 11.457 in

 Main Cable Diameter, maximum
 21 mm | 0.827 in

Dimension Drawing



		GCOG2-DC6	GCOG2-DD6	GCOG2-DE6
Dimensions	L (excl. trigger)	568	645	753
	D	247	247	247
	D with clamp	291	291	291

Splicing Configuration

	GCOG2-DC6		GCOG2-DD6		GCOG2-DE6	
	Fibers	Trays	Fibers	Trays	Fibers	
Single Circuit Splicing Capacity	80	40	144	72	208	104
Single Element Splicing Capacity	240	20	432	36	624	52
R4/R8 Splicing Capacity	160	20	288	36	416	52
R12 Splicing Capacity	144	12	288	24	384	32

Ordering Tree



CX1638-000 | FIST-GCOG2-DD6-NN



Material Specifications

Material Type Impact-resistant polymer

Environmental Specifications

Environmental SpaceBelow ground| BuriedQualification StandardsIEC 61300, 5 m waterhead

Packaging and Weights

Packaging quantity

Packaging TypeBox | CartonWeight, net5.5 kg | 12.125 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

@2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its

trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024

affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names,





Page 3 of 3