

PWRT-208-S

HELIAX® Remote Radio Head Power Cable, 2 conductor with shield, 8 AWG (8.37 mm²), one Red Conductor and one Black Conductor



Product Classification

Regional Availability	North America
Product Type	Power cable
Product Brand	HELIAX®
Product Series	PWRT
Ordering Note	ANDREW® non-standard product

General Specifications

Cable Type	Power
Conductor Type, singles	Stranded
Conductors, quantity	2
Construction Type	Discrete power cable Non-armored
Ground Wire Type	Stranded
Jacket Color	Black
Jacket Color, singles	Black Red
Supported Application	Industrial


Dimensions

Diameter Over Conductor, singles, specific	0.1570 in per 168 strands
Diameter Over Dielectric	6.147 mm 0.242 in
Diameter Over Drain Wire, specific	2.5700 in per 7 strands
Diameter Over Ground Wire	3.2 mm 0.126 in
Diameter Over Jacket, nominal	16.154 mm 0.636 in
Diameter Over Jacket, maximum	16.434 mm 0.647 in
Diameter Over Shield (Braid)	11.938 mm 0.47 in
Jacket Thickness	1.143 mm 0.045 in
Conductor Gauge, singles	8 AWG

PWRT-208-S

Drain Wire Gauge	12 AWG
Ground Wire Gauge	10 AWG
Outer Shield (Braid) Gauge	36 AWG

Cross Section Drawing



Electrical Specifications

Conductor dc Resistance	2.198 ohms/km 0.67 ohms/kft
Conductor dc Resistance Note	Maximum value based on a standard condition of 20 °C (68 °F)
Safety Voltage Rating	600 V

Material Specifications

Conductor Material	Tinned copper
Dielectric Material	PVC
Drain Wire Material	Tinned copper
Filler Material	Polypropylene
Ground Wire Material	Tinned copper
Insulation Material, singles	PVC
Jacket Material	PVC
Outer Shield (Braid) Coverage	65 %
Outer Shield (Braid) Material	Tinned copper
Outer Shield (Tape) Material	Aluminum/Poly, non-bonded

PWRT-208-S

Environmental Specifications

Operating Temperature	-40 °C to +90 °C (-40 °F to +194 °F)
Environmental Space	UV resistant for outdoor and/or direct burial installations
Safety Standard	NEC Article 336 (Type TC)

Packaging and Weights

Cable weight	431.568 kg/km 290 lb/kft
---------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable