CZ4661-000 | FIST-GC02-BD8-GV



FIST® GCO2 Fiber Optic Splice Closure, Heat Shrink or Gold Gel Cable sealing, size BD, no pre-installed fiber trays, 8 round ports + 2 oval ports, with test valve

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Universal mounting system (UMS) profiles provide foundation for mounting combinations of FIST splice trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability	EMEA		
Product Type	Single-ended, round fiber closure		
Product Brand	FIST®		
Product Series	FIST-GC02		
General Specifications			
Cable Entry Drop Port Style	Round		
Cable Entry Main Port Style	Oval		
Cable Ports Quantity, total	2 oval port (2x2 cables) + 8 round ports		
Cable Sealing Type	Gel kit (optional) Heat shrink		
Closure Sealing Type	Dome-to-base clamp with O-ring		
Closure Style	Single-ended		
Color	Black		
Flash Test Valve	Pre-installed		
Ground Feed-through	Included		
Mounting	Pole Strand Wall		
Network Area Type	Distribution		
Splice Tray Included, quantity	0		
Splice Tray Type Included	No trays		
Splicing Capacity, Mass Fusion, maximum	1440		
Splicing Capacity, Single Fusion, maximum	960		
Splicing Type, Supported	Mass fusion Single fusion		

Page 1 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024




CZ4661-000 | FIST-GC02-BD8-GV

Dimensions

Length	566 mm 22.283 in
Cable Entry Drop Port Diameter	30 mm (1.18 in) mm
Diameter	247 mm 9.724 in
Diameter, with clamp	285 mm 11.22 in
Main Cable Diameter, maximum	25 mm 0.984 in

Dimension Drawing



	FIST-GCO2-B <u>C</u>	FIST-GCO2-B <u>D</u>	FIST-GCO2-B <u>E</u>	FIST-GCO2-B <u>F</u>
Length L	488 mm/19.213 in	566 mm/22.283 in	680 mm/26.772 in	795 mm/31.30 in
Width D at base	247 mm/9.724 in	247 mm/9.724 in	247 mm/9.724 in	247 mm/9.724 in
Width D at base with clamp	285 mm/11.22 in	285 mm/11.22 in	285 mm/11.22 in	285 mm/11.22 in

Port Configuration

	Cables per port Cable Diameter, min Cable Dia		Cable Diameter, max
1 Oval Port	2	12 mm / 0.472 in	25 mm / 0.984 in
8 Round Ports	1	5 mm / 0.197 in	30 mm / 1.181 in

Splicing Configuration

Page 2 of 4


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



CZ4661-000 | FIST-GC02-BD8-GV

	FIST-GCO2-B <u>C</u>	FIST-GCO2-BD	FIST-GCO2-B <u>E</u>	FIST-GCO2-B <u>F</u>
UMS Units	2x28	2x42	2x58	2x64
# SC/SLE 4mm trays	56	80	112	128
# SE 8mm trays	28	40	56	64
# R12 12mm Flat ribbon trays	18	26	36	42
Max single splice capacity SC trays (4F/tray)	224	320	448	512
Max single splice capacity SE trays (12F/SE)	336	480	672	768
Max single splice capacity High dense tray (12F/SLE)	672	960	1344	1536
Max mass splice capacity R12 trays (Flat ribbon)	432	624	864	1008
Max mass splice capacity SE trays (Rollable ribbon G657A2 fiber)	1008	1440	1728	1728

Ordering Tree



Material Specifications

Material Type

Packaging Type

Round ports

Impact-resistant polymer

Environmental Specifications

(8 : ø 20) + 1 oval port (8 : ø 13.5)

Below ground Buried		
s IEC 61300, 5 m waterhead		
Flash test valve at 5 psi (40 kPa)		
1		

Box | Carton

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



CZ4661-000 | FIST-GCO2-BD8-GV

Weight, net

4.4 kg | 9.7 lb

Regulatory Compliance/Certifications

Classification

CHINA-ROHS ISO 9001:2015

100 900 1.201

REACH-SVHC

ROHS

UK-ROHS



Below maximum concentration value Designed, manufactured and/or distributed under this quality management system Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant

Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024

