## CJ9790-000 | FIST-GC02-FC6-GV



FIST® GCO2 Fiber Optic Splice Closure, Heat Shrink or Gold Gel Cable sealing, size FC, no pre-installed fiber trays, 6 round ports + 1 oval port, with test valve and grounding option

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Universal mounting system (UMS) profiles provide foundation for mounting combinations of FIST splice trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

#### **Product Classification**

Regional Availability EMEA

**Product Type** Single-ended, rectangular fiber closure

Product Brand FIST®

Product Series FIST-GC02

General Specifications

 Cable Entry Drop Port Style
 Round

 Cable Entry Main Port Style
 Oval

Cable Ports Quantity, total 1 oval port (2 cables) + 6 round ports

Cable Sealing Type Gel kit (optional) | Heat shrink

Closure Sealing Type

Base and dome sealed with latches and O-ring system

Closure Style Single-ended

**Color** Black

Flash Test Valve Pre-installed
Ground Feed-through Included

Mounting Pole | Strand | Wall

Network Area Type Distribution

Splice Tray Included, quantity

Splice Tray Type Included No trays

Splicing Capacity, Mass Fusion, maximum 288
Splicing Capacity, Single Fusion, maximum 384

Splicing Type, Supported Mass fusion | Single fusion

Page 1 of 3



# CJ9790-000 | FIST-GC02-FC6-GV

#### **Dimensions**

 Height
 279 mm | 10.984 in


 Width
 150 mm | 5.906 in

 Length
 384 mm | 15.118 in

 Cable Entry Drop Port Diameter
 30 mm (1.18 in) mm

 Main Cable Diameter, maximum
 25 mm | 0.984 in

### Dimension Drawing




### Splicing Configuration

	FC	FD
UMS Units	16	24
# SC/SLE 4mm trays		16 24
# SE 8mm trays		8 12
# SHD 4mm trays		16 24
# R12 12mm FLAT ribbon trays		5 8
Max. Single splice capacity SC trays (4F/SC)	(	54 96
Max. Single splice capacity high dense trays (12F/SLE)	19	288
Max. Single splice capacity SE trays (12F/SE)	9	96 144
Max. Single splice capacity Super high dense trays (24F/SHD)	38	576
Max. mass splice capacity R12 trays (FLAT ribbon)	13	20 192
Max. mass splice capacity SE trays (Rollable ribbon G657A2 fiber)	28	38 432

## Ordering Tree



# CJ9790-000 | FIST-GC02-FC6-GV



### Material Specifications

Material Type Impact-resistant polymer

### **Environmental Specifications**

Environmental SpaceBelow ground| BuriedQualification StandardsIEC 61300, 5 m waterhead

**Water Resistance** Flash test valve at 5 psi (40 kPa)

### Packaging and Weights

Packaging quantity 1

Packaging TypeBox | CartonWeight, net3.3 kg | 7.275 lb

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

