

# D84435-000 | FIST-GPST-12-APN-2-NS

---



FIST GPST Fiber Termination/Splice Tray, 12/24 ports, no adapters, SMOUV splice chip, 19 in, gray, right patch cord routing

## Product Classification

|                              |                         |
|------------------------------|-------------------------|
| <b>Regional Availability</b> | EMEA                    |
| <b>Product Type</b>          | Fiber patch/splice tray |
| <b>Product Brand</b>         | FIST®                   |
| <b>Product Series</b>        | FIST-GPST               |

## General Specifications

|                                  |                                  |
|----------------------------------|----------------------------------|
| <b>Functionality</b>             | Patching   Splicing              |
| <b>Color</b>                     | Gray                             |
| <b>Interface, front</b>          | Unloaded                         |
| <b>Patch Cord Entry Location</b> | Front, right side                |
| <b>Splicing Type</b>             | Heat shrink, single fiber fusion |
| <b>Total Ports, quantity</b>     | 12                               |

## Dimensions

|               |                    |
|---------------|--------------------|
| <b>Height</b> | 18 mm   0.709 in   |
| <b>Width</b>  | 355 mm   13.976 in |
| <b>Depth</b>  | 190 mm   7.48 in   |

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -5 °C to +45 °C (+23 °F to +113 °F)  |
| <b>Storage Temperature</b>   | -30 °C to +60 °C (-22 °F to +140 °F) |

# D84435-000 | FIST-GPST-12-APN-2-NS

---

**Relative Humidity** Up to 93%, non-condensing

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

**Agency**

REACH-SVHC

**Classification**

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)