

FMT-GVS000000-E96P



FMT Fiber Optic MicroVAM Panel, 16 module capacity, 2RU, 19 in, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber VAM panel
Product Series	FMT

General Specifications

Functionality	Multiplexing Patching Splitting
Body Style	Symmetrical
Color	Black + Putty white (front)
Growth Configuration	Unloaded
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	16
Rack Type	EIA 19 in EIA 23 in
Rack Units	2
Shelf Movement	Sliding
Total Ports, quantity	0

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	305 mm 12.008 in

Material Specifications

Finish	Powder coated
Material Type	Steel

FMT-GVS000000-E96P

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

