

FPS-SPB1ANJ



FCM/FL2 wideVAM Fiber Optic Splitter Module, 1 x 32, SC/UPC input, SC /APC output, singlemode

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Splitter module
Product Series	FDF

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Access	Rear
Application	For use with FDF frames For use with FL2 panels
Circuits, quantity	1
Distribution Type	1 x 32 splitter
Interface, front	SC/APC
Interface, Input	SC/UPC
Interface, Output	SC/APC
Interface, rear	SC/UPC
Module Color	Putty white
Split Ratio	Symmetrical
Splitter, quantity	1

Optical Specifications

Directivity, minimum	55 dB
Polarization Dependent Loss, maximum	0.3 dB
Uniformity, maximum	1.3 dB
Insertion Loss, Splitter, maximum	16.7 dB
Insertion Loss, Splitter, typical	16.5 dB

FPS-SPB1ANJ

Return Loss, Splitter, minimum 55 dB

Environmental Specifications

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

