300001780247 | FD3-AC144J2AJABP1P



FDH 3000 Fiber Distribution Extra Small Pole Mount Cabinet, 144F, SC /APC, (2) 32-splitter module, die. LT, 100 ft, 12F

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000
General Specifications	
Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	2
Distribution Ports, quantity	144
Fibers per Distribution Cable, quantity	72
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole
Split Ratio	Symmetrical
Splitter Slots, quantity	9
Splitter Type	1 x 32
Splitter, quantity	2
Dimensions	
Height	762 mm 30 in
Width	533 mm 20.984 in
Depth	356 mm 14.016 in
Cable Length	30.48 m 100 ft
Enclosure Size	Extra small

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 18, 2024



300001780247 | FD3-AC144J2AJABP1P

Material Specifications

Finish

Material Type

Powder coated

Aluminum

Environmental Specifications

Environmental SpaceAerialPackaging and Weights1Packaging quantity1Packaging TypePalletRegulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 18, 2024

