

# NGF-CB2MR221126

---



Next Generation Frame (NGF) Fiber Termination/Splice Block, pre-terminated, 144 FC/UPC, singlemode, left oriented, putty white

## OBSOLETE

This product was discontinued on: **March 1, 2018**

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Fiber patch/splice block
<b>Product Series</b>	NGF

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Application</b>	Used in NGF-style frames only
<b>Body Style</b>	Right orientation
<b>Cable Exit Location</b>	Rear, bottom side
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Door Type, front</b>	Compression latch   Hinged
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	FC/UPC
<b>Rack Type</b>	NGF
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	144

## Dimensions

<b>Height</b>	558.8 mm   22 in
---------------	------------------

# NGF-CB2MR221126

---

**Width** 166.878 mm | 6.57 in

**Depth** 495.3 mm | 19.5 in

## Material Specifications

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Operating Temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 80%, non-condensing

**Qualification Standards** Telcordia GR-449-CORE

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

