



SYSTIMAX 360™ iPatch® G2 Multimode OM1 High Density Module

## OBSOLETE

This product was discontinued on: March 1, 2018

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	OptiSPEED®   SYSTIMAX 360™   iPatch®

## General Specifications

<b>Functionality</b>	Breakout
<b>Adapters, quantity, rear</b>	4
<b>Color, front</b>	Beige
<b>Color, housing</b>	Black
<b>Color, rear</b>	Black
<b>Intelligence Type</b>	iPatch® enabled
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Reduced footprint
<b>Total Ports, quantity, front</b>	48

## Dimensions

<b>Height</b>	82.55 mm   3.25 in
<b>Width</b>	152.4 mm   6 in
<b>Depth</b>	215.9 mm   8.5 in

## Material Specifications

# 760093385 | 360-iP-HD-MOD-LC-05

**Material Type** Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC)

## Optical Specifications

**Fiber Type** OM1  
**Insertion Loss Change, mating** 0.3 dB  
**Insertion Loss Change, temperature** 0.3 dB  
**Insertion Loss, maximum** 0.85 dB

## Environmental Specifications

**Operating Temperature** -5 °C to +50 °C (+23 °F to +122 °F)  
**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)  
**Relative Humidity** Up to 95%, non-condensing  
**Flammability Rating** UL 94 V-0  
**Safety Standard** ACMA | CE | UL | cUL

## Packaging and Weights

**Packaging quantity** 1  
**Weight, net** 1.13 kg | 2.491 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



### \* Footnotes

**Insertion Loss Change, mating** Maximum insertion loss change after 500 matings  
**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)