


FDT-AN012NXT9500



iFDT Indoor Fiber Distribution Terminal, 12-fiber, SC/UPC, loose tube OSP cable, 9500 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Series	IFDT

General Specifications


Adapters, quantity	12
Cable Entry Location	Bottom right Top right
Cable Type	OSP - Loose Tube
Color	Putty white
Front Door Type	Double hinged
Growth Configuration	Fully loaded
Interface	SC/UPC
Interface, stub	No connector
Lock Type	Padlock ready
Mounting	Wall
Port, quantity	12

Dimensions

Height	184.15 mm 7.25 in
Width	299.72 mm 11.8 in
Depth	82.55 mm 3.25 in
Cable Length	2,895.6 m 9500 ft

Ordering Tree

FDT-AN012NXT9500



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity 1

FDT-AN012NXT9500

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

