



## SYSTIMAX 360™ GigaSPEED X10D® Evolve High Density Shielded Angled Modular Panel, 24 port

### Product Classification

#### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

#### Portfolio

SYSTIMAX®

#### Product Type

RJ45 patch panel

#### Product Brand

GigaSPEED X10D® | SYSTIMAX 360™

#### Product Series

HGS Series

### General Specifications

#### ANSI/TIA Category

6A

#### Cable Type

Shielded

#### Color

Cool gray | Satin chrome

#### Conductor Type

Solid | Stranded

#### Intelligence Type

iPatch® ready

#### Panel Style

Angled

#### Rack Type

EIA 19 in

#### Rack Units

1

#### Termination Type

IDC

#### Total Ports, quantity

24

#### Transmission Standards

ANSI/TIA-568-D.2 | ISO/IEC 11801 Class E

#### Wiring

T568A | T568B

### Dimensions

#### Height

44.45 mm | 1.75 in

#### Width

482.6 mm | 19 in

#### Depth, with cable management

266.7 mm | 10.5 in

#### Compatible Conductor Gauge, solid

22 AWG | 24 AWG

# 760151290 | 360-IPR-MFTPA-E-HD6B-1U-24

**Compatible Conductor Gauge, stranded**

22 AWG | 24 AWG

## Electrical Specifications

**Dielectric Withstand Voltage, RMS, contact-to-contact**

1,000 Vac @ 60 Hz

**Insulation Resistance, minimum**

500 MOhm

## Material Specifications

**Contact Plating Material**

Precious metals

**Material Type**

High-impact, flame retardant, thermoplastic | Powder-coated steel

**Termination Contact Plating**

Nickel

## Mechanical Specifications

**Plug Insertion Life, minimum**

750 times

**Plug Insertion Life, test plug**

IEC 60603-7 compliant plug

**Plug Retention Force, minimum**

133 N | 29.9 lbf

## Environmental Specifications

**Operating Temperature**

-10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature**

-40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity**

Up to 95%, non-condensing

**Flammability Rating**

UL 94 V-0

**Safety Standard**

UL | cUL

## Packaging and Weights

**Packaging quantity**

1

**Weight, net**

0.839 kg | 1.85 lb

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

